

VELP Scientifica Solutions for Heating & Stirring



ARE

AREX

ARED

AM4

T.ARE

AREC

AREC.X

HSC

AREC.T

		ARE	AREX	ARED	AM4	T.ARE	AREC	AREC.X	HSC	AREC.T
Heating plate		Aluminum alloy	Aluminum alloy	Aluminum alloy	Aluminum alloy	Aluminum alloy	Ceramic	Ceramic	Ceramic	Ceramic
Heating plate dimensions	mm	∅ 155	∅ 155	∅ 180	∅ 155	∅ 180	180x180	180x180	180x180	180x180
	(in)	∅ 6.1	∅ 6.1	∅ 7.1	∅ 6.1	∅ 7.1	7.1x7.1	7.1x7.1	7.1x7.1	7.1x7.1
Stirring speed rpm		up to 1200	up to 1200	up to 1200	up to 1200	up to 1200	up to 1300	up to 1300	up to 1300	up to 1300
Stirring volume L		up to 15	up to 20	up to 25	up to 20	up to 25	up to 15	up to 15	up to 15	up to 15
Temperature regulation °C		Ambient to 370	Ambient to 370	Ambient to 370	Ambient to 370	Ambient to 370	Ambient to 540	Ambient to 540	Ambient to 540	Ambient to 540
Overtemperature protection		•	•	•	•	•	•	•	•	•
Counter reaction							•	•		•
Dimensions (WxHxD) mm		165x115x280	165x115x280	190x110x245	715x115x220	190x110x245	225x96x335	225x96x335	225x96x335	225x96x335
	(in)	(6.5x4.5x11.0)	(6.5x4.5x11.0)	(7.5x4.3x9.6)	(28.1x4.5x8.7)	(7.5x4.3x9.6)	(8.0x3.7x13.2)	(8.0x3.7x13.2)	(8.0x3.7x13.2)	(8.0x3.7x13.2)
Weight	Kg	2.6	2.6	3.1	8.3	3.1	3.9	3.9	3.9	3.9
	(lb)	(5.7)	(5.7)	(6.8)	(18.2)	(6.8)	(8.6)	(8.6)	(8.6)	(8.6)
Power Supply		115 or 230 V	115 or 230 V	115 or 230 V	230 V	115 or 230 V	115 or 230 V	115 or 230 V	115 or 230 V	115 or 230 V
Power		630 W	630 W	900 W	2550 W	900 W	800 W	800 W	800 W	800 W



www.velp.com